

PLUSVAC 21



Standard equipment

- Cylinder sealing
- Sealing bars are to remove without tools
- Wide double sealing
- Lid locking can be unhooked
- Dynamic end position damping of the lid opening
- Vacuum-moulded chambers, hygienic cleaning
- Silent ventilation
- Grip protection on the lid
- Recessed control board
- Robust components and construction
- Stainless steel as well as best metal alloys
- Plexiglas lid – important for packaging soups and sauces
- Service program for the pump
- Oil change indicator
- Optimised heat dissipation
- Vacuum stop button
- Microcomputer control board
- Inlet plates for height adjustment
- Convex plexiglas lid

Selectable options

- Gas flushing (MAP)
- Program control with sensor (Perfect)
- Connection for external extraction (container)
- Cut-off and sealing
- Compressed air pressure sealing, external air compressor required
- Switch off sealing bar
- Additional sealing bar
- Bigger vacuum pumps
- Voltage variants
- ESD-Version
- Stronger sealing transformer
- Plug with phase inverter

Technical data

Chamber size (w x l x h / mm)	430 x 505 x 175
Control board	
• Standard	Comfort
• Option	Perfect
Sealing length (mm)	1 x 405 (2 x 405)
Sealing seam	double
Distance x (mm)	455 (400)
Position of sealing bar	
• Standard	front
• Option	back
Pump (cbm/h)	21 (40 / 60)
Power connection	400V/3Ph+N+PE/50Hz
Power from (kW)	1.1 (1.6/1.9)
Max. bag (mm)	400 x 500
Insert plates	2
Outer dimensions (lid closed / w x d x h/mm)	480 x 655 x 975
Outer dimensions (lid open / w x d x h/mm)	480 x 655 x 1,550
Weight (kg)	65 (95 / 97)

The data in brackets are options.

